

ACCESSORIES

UL/NEMA/IEC



Internal Panels for PN Series Plastic NEMA 4 Boxes

Aluminum internal panels for PN series plastic boxes are used to mount equipment inside the enclosures. Assembles to mounting bosses on inside of enclosure.

- Designed to fit PN series plastic NEMA boxes
- 0.062-inch-thick aluminum
- Panel mounting hardware included

| Catalog No. | Length × Width × Thickness (Inches) | Fits Enclosure |
|-------------|-------------------------------------|--|
| PNX-91420 | 2.17 × 1.93 × 0.06 | PN-1320, PN-1320-DG, PN-1320-C, PN-1320-MB, PN-1320-DGMB |
| PNX-91421 | 4.06 × 2.09 × 0.06 | PN-1321, PN-1321-DG, PN-1321-C, PN-1321-MB, PN-1321-DGMB, PN-1322, PN-1322-DG, PN-1322-C, PN-1321-MB, PN-1322-DGMB |
| PNX-91423 | 4.02 × 3.03 × 0.06 | PN-1323, PN-1323-DG, PN-1323-C, PN-1323-MB, PN-1323-DGMB, PN-1328, PN-1328-DG, PN-1328-C, PN-1328-MB, PN-1328-DGMB |
| PNX-91424 | 6.26 × 4.29 × 0.06 | PN-1324, PN-1324-DG, PN-1324-C, PN-1324-MB, PN-1324-DGMB, PN-1327, PN-1327-DG, PN-1327-C, PN-1327-MB, PN-1327-DGMB |
| PNX-91425 | 8.27 × 5.27 × 0.06 | PN-1325, PN-1325-DG, PN-1325-C, PN-1325-MB, PN-1325-DGMB, PN-1329, PN-1329-DG, PN-1329-C, PN-1329-MB, PN-1329-DGMB |
| PNX-91426 | 7.32 × 2.8 × 0.06 | PN-1326, PN-1326-DG, PN-1326-C, PN-1326-MB, PN-1326-DGMB |
| PNX-91430 | 1.71 × 1.63 × 0.06 | PN-1330, PN-1330-DG, PN-1330-C |
| PNX-91431 | 2.87 × 2.8 × 0.06 | PN-1331, PN-1331-DG, PN-1331-C |
| PNX-91432 | 5.91 × 2.76 × 0.06 | PN-1332, PN-1332-DG, PN-1332-C, PN-1333, PN-1333-DG, PN-1333-C |
| PNX-91434 | 7.50 × 4.35 × 0.06 | PN-1334, PN-1334-DG, PN-1334-C, PNR-2604, PNR-2604-DG, PNR-2604-C |
| PNX-91435 | 10.02 × 6.87 × 0.06 | PN-1335, PN-1335-DG, PN-1335-C |
| PNX-91436 | 4.29 × 4.29 × 0.06 | PN-1336, PN-1336-DG, PN-1336-C, PN-1337, PN-1337-DG, PN-1337-C |
| PNX-91438 | 5.87 × 5.87 × 0.06 | PN-1338, PN-1338-DG, PN-1338-C, PN-1339, PN-1339-DG, PN-1339-C |
| PNX-91440 | 8.98 × 5.83 × 0.06 | PN-1340, PN-1340-DG, PN-1340-C, PN-1341, PN-1341-DG, PN-1341-C |
| PNX-91442 | 11.37 × 8.62 × 0.06 | PN-1342, PN-1342-DG, PN-1342-C, PN-1343, PN-1343-DG, PN-1343-C |
| PNX-91444 | 13.65 × 7.35 × 0.06 | PN-1344, PN-1344-DG, PN-1344-C |
| PNX-92600 | 3.58 × 3.58 × 0.06 | PNR-2600, PNR-2600-DG, PNR-2600-C, PNR-2601, PNR-2601-DG, PNR-2601-C |
| PNX-92602 | 4.37 × 2.8 × 0.06 | PNR-2602, PNR-2602-DG, PNR-2602-C, PNR-2603, PNR-2603-DG, PNR-2603-C |
| PNX-92605 | 9.07 × 4.36 × 0.06 | PNR-2605, PNR-2605-DG, PNR-2605-C |
| PNX-92607 | 7.52 × 5.55 × 0.06 | PNR-2607, PNR-2607-DG, PNR-2607-C, PNR-2608, PNR-2608-DG, PNR-2608-C |



Internal Panels for Die-Cast Aluminum NEMA 4 Boxes

Aluminum Internal Panels for AN series boxes. Used to mount customer equipment inside the enclosures. Assembles to mounting bosses on inside of enclosure.

- Designed to fit AN series die-cast aluminum NEMA boxes
- 0.062-inch-thick aluminum
- Panel mounting hardware included

| Catalog No. | Length × Width × Thickness (Inches) | Fits Enclosure |
|-------------|-------------------------------------|--|
| ANX-91300 | 3.07 × 0.95 × 0.06 | AN-1300, AN-1300-G, AN-2800, AN-2800-B, AN-2850, AN-2850-B |
| ANX-91301 | 2.13 × 1.87 × 0.06 | AN-1301, AN-1301-G, AN-2801, AN-2801-B, AN-2851, AN-2851-B |
| ANX-91302 | 4.06 × 2.09 × 0.06 | AN-1302, AN-1302-G, AN-2802, AN-2802-B, AN-2852, AN-2852-B, AN-1303, AN-1303-G, AN-2803, AN-2803-B AN-2853, AN-2853-B |
| ANX-91304 | 4.04 × 3.05 × 0.06 | AN-1304, AN-1304-G, AN-2804, AN-2804-B, AN-2854, AN-2854-B |
| ANX-91305 | 5.37 × 3.79 × 0.06 | AN-1305, AN-1305-G, AN-2805, AN-2805-B, AN-2855, AN-2855-B |
| ANX-91306 | 6.23 × 4.26 × 0.06 | AN-1306, AN-1306-G, AN-2806, AN-2806-B, AN-2856, AN-2856-B |
| ANX-91307 | 8.3 × 5.3 × 0.06 | AN-1307, AN-1307-G, AN-2807, AN-2807-B, AN-2857, AN-2857-B, AN-1308, AN-1308-G, AN-2808, AN-2808-B, AN-2858, AN-2858-B |
| ANX-91309 | 4.02 × 4.02 × 0.06 | AN-1309, AN-1309-G, AN-2809, AN-2809-B |
| ANX-91310 | 5.52 × 5.52 × 0.06 | AN-1310, AN-1310-G, AN-2810, AN-2810-B |
| ANX-91311 | 1.7 × 1.5 × 0.06 | AN-1311, AN-1311-G, AN-2811, AN-2811-B |
| ANX-91312 | 3.5 × 2.16 × 0.06 | AN-1312, AN-1312-G, AN-2812, AN-2812-B |
| ANX-91313 | 4.48 × 2.72 × 0.06 | AN-1313, AN-1313-G, AN-2813, AN-2813-B, AN-1314, AN-1314-G, AN-2814, AN-2814-B |
| ANX-91315 | 5.53 × 2.15 × 0.06 | AN-1315, AN-1315-G, AN-2815, AN-2815-B |
| ANX-91316 | 5.79 × 3.43 × 0.06 | AN-1317, AN-1317-G, AN-2817, AN-2817-B |
| ANX-91318 | 1.81 × 1.30 × 0.06 | AN-1318, AN-1318-G, AN-2818, AN-2818-B |
| ANX-91319 | 2.72 × 2.50 × 0.06 | AN-1319, AN-1319-G, AN-2819, AN-2819-B |
| ANX-91320 | 3.66 × 1.69 × 0.06 | AN-1320, AN-1320-G, AN-2820, AN-2820-B |
| ANX-91321 | 6.52 × 2.78 × 0.06 | AN-1321, AN-1321-G, AN-2821, AN-2821-B |
| ANX-91322 | 7.43 × 4.27 × 0.06 | AN-1322, AN-1322-G, AN-2822, AN-2822-B |
| ANX-91323 | 9.72 × 5.79 × 0.06 | AN-1323, AN-1323-G, AN-2823, AN-2823-B |